

06504.0-00 Cut Sheet



Stego enclosure heater, 150W heating capacity, touch-safe PTC resistor heating element, 120-240 VAC/VDC operating voltage, 50/60 Hz, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/06504.0-00>

Technical Specifications

| | |
|--------------------------|---|
| Brand | Stego |
| Item | Enclosure heater |
| IP Rating | IP20 |
| Heating Capacity | 150W |
| Heating Element | Touch-safe PTC resistor |
| Operating Voltage | 120-240 VAC/VDC |
| Hertz | 50/60 Hz |
| Connection | Pressure clamps for (2) 14 AWG max stranded (with wire ferrule) or solid wire |
| Mounting | 35mm DIN rail or panel |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E234324 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/06504.0-00.pdf>
See store item page for other formats.