

# 086010-00 Cut Sheet



Stego filter, replacement, 4.65 x 4.65in, synthetic fiber, washable, G4 (coarse). Package of 3. For use with 4.88 x 4.88in Stego Filter Fan Plus fans and intake grilles and 4.92 x 4.92in Stego Filter Fan fans and exhaust grilles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/086010-00>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Filter
<b>Replacement</b>	Yes
<b>Size</b>	4.65 x 4.65in
<b>Filter Element</b>	Synthetic fiber
<b>Washable</b>	Yes
<b>Average Arrestance</b>	94%
<b>Filter Density</b>	350 g/m2
<b>Filter Rating</b>	G4 (coarse)
<b>Other Filter Characteristics</b>	Temperature resistant to 212F, moisture resistant to 100% RH
<b>Quantity per Pack</b>	3
<b>For Use With</b>	4.88 x 4.88in Stego Filter Fan Plus fans and intake grilles and 4.92 x 4.92in Stego Filter Fan fans and exhaust grilles

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>