

086030-00 Cut Sheet



Stego filter, replacement, 3.50 x 3.50in, synthetic fiber, washable, M5 (medium). Package of 3. For use with 3.82 x 3.82in Stego Filter Fan fans and exhaust grilles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/086030-00>

Technical Specifications

Brand	Stego
Item	Filter
Replacement	Yes
Size	3.50 x 3.50in
Filter Element	Synthetic fiber
Washable	Yes
Average Arrestance	98%
Filter Density	360 g/m2
Filter Rating	M5 (medium)
Other Filter Characteristics	Temperature resistant to 212F, moisture resistant to 100% RH
Quantity per Pack	3
For Use With	3.82 x 3.82in Stego Filter Fan fans and exhaust grilles

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document