

# 086040-00 Cut Sheet



Stego filter, replacement, 4.65 x 4.65in, synthetic fiber, washable, M5 (medium). Package of 3. For use with 4.88 x 4.88in Stego Filter Fan Plus fans and intake grilles and 4.92 x 4.92in Stego Filter Fan fans and exhaust grilles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/086040-00>

## Technical Specifications

|                    |                 |
|--------------------|-----------------|
| Brand              | Stego           |
| Item               | Filter          |
| Replacement        | Yes             |
| Size               | 4.65 x 4.65in   |
| Filter Element     | Synthetic fiber |
| Washable           | Yes             |
| Average Arrestance | 98%             |
| Filter Density     | 360 g/m2        |

|                              |   |
|------------------------------|---|
| Filter Rating                | M5 (medium)   |
| Other Filter Characteristics | Temperature resistant to 212F, moisture resistant to 100% RH  |
| Quantity per Pack            | 3   |
| For Use With                 | 4.88 x 4.88in Stego Filter Fan Plus fans and intake grilles and 4.92 x 4.92in Stego Filter Fan fans and exhaust grilles |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | E234324                                |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |