

086050-00 Cut Sheet



Stego filter, replacement, 6.61 x 6.61in, synthetic fiber, washable, M5 (medium). Package of 3. For use with 6.93 x 6.93in Stego Filter Fan fans and exhaust grilles, Filter Fan Plus fans, and Filter Fan Plus FPO intake grilles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/086050-00>

Technical Specifications

Brand	Stego
Item	Filter
Replacement	Yes
Size	6.61 x 6.61in
Filter Element	Synthetic fiber
Washable	Yes
Average Arrestance	98%
Filter Density	360 g/m2

Filter Rating	M5 (medium)
Other Filter Characteristics	Temperature resistant to 212F, moisture resistant to 100% RH
Quantity per Pack	3
For Use With	6.93 x 6.93in Stego Filter Fan fans and exhaust grilles, Filter Fan Plus fans, and Filter Fan Plus FPO intake grilles

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document