


# 086300-00 Cut Sheet



Stego filter, replacement, 3.31 x 3.31in, synthetic fiber, washable, M5 (medium). Package of 3. For use with 3.62 x 3.62in Stego Filter Fan Plus fans and intake grilles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/086300-00>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Filter
<b>Replacement</b>	Yes
<b>Size</b>	3.31 x 3.31in
<b>Filter Element</b>	Synthetic fiber
<b>Washable</b>	Yes
<b>Average Arrestance</b>	98%
<b>Filter Density</b>	360 g/m2
<b>Filter Rating</b>	M5 (medium)
<b>Other Filter Characteristics</b>	Temperature resistant to 212F, moisture resistant to 100% RH
<b>Quantity per Pack</b>	3
<b>For Use With</b>	3.62 x 3.62in Stego Filter Fan Plus fans and intake grilles

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>