

086350-00 Cut Sheet



Stego filter, replacement, 6.61 x 6.61in, synthetic fiber, washable, G3 (coarse). Package of 5. For use with 6.93 x 6.93in Stego Filter Fan fans and exhaust grilles, Filter Fan Plus fans, and Filter Fan Plus FPO intake grilles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/086350-00>

Technical Specifications

Brand	Stego
Item	Filter
Replacement	Yes
Size	6.61 x 6.61in
Filter Element	Synthetic fiber
Washable	Yes
Average Arrestance	84%
Filter Density	200 g/m2

Filter Rating	G3 (coarse)
Other Filter Characteristics	Temperature resistant to 212F, moisture resistant to 100% RH
Quantity per Pack	5
For Use With	6.93 x 6.93in Stego Filter Fan fans and exhaust grilles, Filter Fan Plus fans, and Filter Fan Plus FPO intake grilles

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document