

086370-00 Cut Sheet



Stego filter, replacement, 11.14 x 11.14in, synthetic fiber, washable, G3 (coarse). Package of 5. For use with 11.46 x 11.46in Stego Filter Fan Plus fans and intake grilles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/086370-00>

Technical Specifications

| | |
|-------------------------------------|--|
| Brand | Stego |
| Item | Filter |
| Replacement | Yes |
| Size | 11.14 x 11.14in |
| Filter Element | Synthetic fiber |
| Washable | Yes |
| Average Arrestance | 84% |
| Filter Density | 200 g/m2 |
| Filter Rating | G3 (coarse) |
| Other Filter Characteristics | Temperature resistant to 212F, moisture resistant to 100% RH |
| Quantity per Pack | 5 |
| For Use With | 11.46 x 11.46in Stego Filter Fan Plus fans and intake grilles |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |