

# 086720-00 Cut Sheet



Stego hose-proof filter fan hood, fits 6.93 x 6.93in fan cutout, stainless steel, sanitary gasket, NEMA 4/4X, IP56, for increasing the protection classification of Stego Filter Fan and Filter Fan Plus fans and grilles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/086720-00>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Hose-proof filter fan hood
<b>Fan Cutout Size</b>	6.93 x 6.93in
<b>Height</b>	14.01in
<b>Width</b>	11.44in
<b>Depth</b>	2.68in
<b>Maximum Covered Area</b>	9.19 x 9.19in (HxW)
<b>Material</b>	Stainless steel
<b>Gasket Type</b>	Sanitary
<b>NEMA Rating</b>	4/4X
<b>IP Rating</b>	IP56
<b>Application</b>	For increasing the protection classification of Stego Filter Fan and Filter Fan Plus fans and grilles

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/086720-00.pdf>  
See store item page for other formats.