

086720-00 Cut Sheet



Stego hose-proof filter fan hood, fits 6.93 x 6.93in fan cutout, stainless steel, sanitary gasket, NEMA 4/4X, IP56, for increasing the protection classification of Stego Filter Fan and Filter Fan Plus fans and grilles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/086720-00>

Technical Specifications

Brand	Stego
Item	Hose-proof filter fan hood
Fan Cutout Size	6.93 x 6.93in
Height	14.01in
Width	11.44in
Depth	2.68in
Maximum Covered Area	9.19 x 9.19in (HxW)
Material	Stainless steel
Gasket Type	Sanitary
NEMA Rating	4/4X
IP Rating	IP56
Application	For increasing the protection classification of Stego Filter Fan and Filter Fan Plus fans and grilles

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document