

# 0908240SBA Cut Sheet

KNIPEX linemans pliers, 9.5in (241mm) overall length, insulated, 1000V insulation rating, precision machined hardened cutting edges, cushion grip handles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/0908240SBA>

## Technical Specifications

<b>Brand</b>	KNIPEX
<b>Item</b>	Pliers
<b>Pliers Type</b>	Lineman's
<b>Overall Length</b>	9.5in (241mm)
<b>Insulated</b>	Yes
<b>Insulation Rating</b>	1000V
<b>Cutting</b>	Precision machined hardened cutting edges
<b>Capacity</b>	1/8in hard wire or 3/16in medium wire
<b>Handle Type</b>	Cushion grip handles
<b>Application</b>	Gripping and wire cutting
<b>Material</b>	Vanadium steel, forged, multi-stage oil-hardened
<b>Applicable Standards</b>	DIN ISO 5746 and ASME B107.20
<b>Additional Information</b>	ASTM F1505-tested

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>