

0911240 Cut Sheet



KNIPEX linemans pliers, 9.5in (241mm) overall length, precision machined hardened cutting edges, plastic coated handles, fishtape puller.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/0911240>

Technical Specifications

Brand	KNIPEX
Item	Pliers
Pliers Type	Lineman's
Overall Length	9.5in (241mm)
Insulated	No
Cutting	Precision machined hardened cutting edges
Capacity	1/8in hard wire or 3/16in medium wire
Handle Type	Plastic coated handles
Application	Gripping, wire cutting, fish tape pulling and crimping
Material	Vanadium steel, forged, multi-stage oil-hardened
Applicable Standards	DIN ISO 5746 and ASME B107.20
Tool Features	Fishtape puller

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement