

0912240SBA Cut Sheet

KNIPEX linemans pliers, 9.5in (241mm) overall length, precision machined hardened cutting edges, KNIPEXTEND comfort handle, KNIPEXTEND color tip and tether compatible and fishtape puller.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/0912240SBA>

Technical Specifications

Brand	KNIPEX
Item	Pliers
Pliers Type	Lineman's
Overall Length	9.5in (241mm)
Insulated	No
Cutting	Precision machined hardened cutting edges
Capacity	1/8in hard wire or 3/16in medium wire
Handle Type	KNIPEXTEND comfort handle
Application	Gripping, wire cutting, fish tape pulling and crimping
Material	Vanadium steel, forged, multi-stage oil-hardened
Applicable Standards	DIN ISO 5746 and ASME B107.20
Tool Features	KNIPEXTEND color tip and tether compatible and fishtape puller

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document