

1-18-1981-070200 Cut Sheet



MP Sensor InLine pressure transmitter, -14.5 to +14.5 psig range, $\pm 0.5\%$ accuracy, silicone sensing element, Output: 1-channel, current, 3/8in push-to-connect process connection, 9–30 VDC operating voltage, 4-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1-18-1981-070200>

Technical Specifications

Brand	MP Sensor
Item	Pressure transmitter
Series	InLine
Media Type	Air and gases
Pressure Range	-14.5 to +14.5 psig
Accuracy	$\pm 0.5\%$ of full range
Wetted Parts	Silicone, PBT, polycarbonate
Housing Material	Polybutylene terephthalate (PBT)/polycarbonate

Sensing Element Material	Silicone
Number Of Output Channels	1
Output	4–20 mA
Process Connection	3/8in push-to-connect
Operating Voltage	9–30 VDC
IP Rating	IP65
Electrical Connection	4-pin M8 quick-disconnect
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E511277
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/1-18-1981-070200.pdf>
See store item page for other formats.