

10.02.01.00566 Cut Sheet



Schmalz basic vacuum ejector, 71.0 l/min (2.5 cfm) suction rate, 6mm push-to-connect inlet(s), 8mm push-to-connect vacuum port.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/10.02.01.00566>

Technical Specifications

Brand	Schmalz
Item	Vacuum ejector
Ejector Type	Basic
Degree of Evacuation	85%
Suction Rate	71.0 l/min (2.5 cfm)
Air Consumption	105.0 l/min (3.7 cfm)
Average Noise Level	65 dbA
Inlet Port	6mm push-to-connect
Vacuum Port	8mm push-to-connect
Air Saving	No
Alternate ID	SBP-15-S02-SDA

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/10.02.01.00566.pdf>
See store item page for other formats.