

# 10.02.01.01597 Cut Sheet

Schmalz basic vacuum ejector, 500.0 l/min (17.7 cfm) suction rate, G3/8 female BSPP inlet(s), G3/4 female BSPP vacuum port.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/10.02.01.01597>

## Technical Specifications

<b>Brand</b>	Schmalz
<b>Item</b>	Vacuum ejector
<b>Ejector Type</b>	Basic
<b>Degree of Evacuation</b>	60%
<b>Suction Rate</b>	500.0 l/min (17.7 cfm)
<b>Air Consumption</b>	160.0 l/min (5.7 cfm)
<b>Average Noise Level</b>	65 dbA
<b>Inlet Port</b>	G3/8 female BSPP
<b>Vacuum Port</b>	G3/4 female BSPP
<b>Air Saving</b>	No
<b>Includes</b>	Mounting hardware
<b>Alternate ID</b>	SBPL-50-HF

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>