

# 100018093024002 Cut Sheet



Mindman air valve manifold, aluminum, clear, 145 psi maximum operating pressure, (2) stations, (2) 1/4in female NPT inlet(s), (4) 1/4in female NPT exhaust(s). For use with MVSC1-180 and MVAA-180 series solenoid directional control valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/100018093024002>

## Technical Specifications

<b>Brand</b>	Mindman
<b>Item</b>	Valve manifold
<b>Working Fluid</b>	Pneumatic
<b>Material</b>	Aluminum
<b>Color</b>	Clear
<b>Number of Stations</b>	2
<b>Maximum Operating Pressure</b>	145 psi
<b>Inlet Port</b>	(2) 1/4in female NPT
<b>Exhaust Port</b>	(4) 1/4in female NPT
<b>For Use With</b>	MVSC1-180 and MVAA-180 series solenoid directional control valves
<b>Includes</b>	Mounting hardware and gaskets

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/100018093024002.pdf>  
See store item page for other formats.