

# 100218091044002 Cut Sheet



Mindman air valve manifold, aluminum, clear, 145 psi maximum operating pressure, (4) stations, (2) 1/4in female NPT inlet(s), (2) 1/4in female NPT exhaust(s). For use with MVSC1-180 and MVAA-180 series solenoid directional control valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/100218091044002>

## Technical Specifications

|                                   |   |
|-----------------------------------|---|
| <b>Brand</b>                      | Mindman   |
| <b>Item</b>                       | Valve manifold  |
| <b>Working Fluid</b>              | Pneumatic   |
| <b>Material</b>                   | Aluminum  |
| <b>Color</b>                      | Clear   |
| <b>Number of Stations</b>         | 4   |
| <b>Maximum Operating Pressure</b> | 145 psi   |
| <b>Inlet Port</b>                 | (2) 1/4in female NPT  |
| <b>Exhaust Port</b>               | (2) 1/4in female NPT  |
| <b>For Use With</b>               | MVSC1-180 and MVAA-180 series solenoid directional control valves |
| <b>Includes</b>                   | Mounting hardware and gaskets                                     |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | None  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/100218091044002.pdf>  
See store item page for other formats.