

100450093024001 Cut Sheet



Mindman air valve manifold, aluminum, clear, 174 psi maximum operating pressure, (2) stations, (2) 1/2in female NPT inlet(s), (4) 1/2in female NPT exhaust(s). For use with MVHB-500 series manual directional control valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/100450093024001>

Technical Specifications

Brand	Mindman
Item	Valve manifold
Working Fluid	Pneumatic
Material	Aluminum
Color	Clear
Number of Stations	2
Maximum Operating Pressure	174 psi
Inlet Port	(2) 1/2in female NPT
Exhaust Port	(4) 1/2in female NPT
For Use With	MVHB-500 series manual directional control valves
Includes	Mounting hardware and gaskets

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/100450093024001.pdf>
See store item page for other formats.