

# 100450093044001 Cut Sheet



Mindman air valve manifold, aluminum, clear, 174 psi maximum operating pressure, (4) stations, (2) 1/2in female NPT inlet(s), (4) 1/2in female NPT exhaust(s). For use with MVHB-500 series manual directional control valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/100450093044001>

## Technical Specifications

|                                   |   |
|-----------------------------------|---|
| <b>Brand</b>                      | Mindman   |
| <b>Item</b>                       | Valve manifold                                    |
| <b>Working Fluid</b>              | Pneumatic   |
| <b>Material</b>                   | Aluminum  |
| <b>Color</b>                      | Clear   |
| <b>Number of Stations</b>         | 4   |
| <b>Maximum Operating Pressure</b> | 174 psi   |
| <b>Inlet Port</b>                 | (2) 1/2in female NPT                              |
| <b>Exhaust Port</b>               | (4) 1/2in female NPT                              |
| <b>For Use With</b>               | MVHB-500 series manual directional control valves |
| <b>Includes</b>                   | Mounting hardware and gaskets                     |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | None  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/100450093044001.pdf>  
See store item page for other formats.