

100815015321002 Cut Sheet



Mindman pneumatic solenoid valve, 5-port (4-way), 2-position, single solenoid internal pilot return, M5 x 0.8 female inlet(s), (2) M5 x 0.8 female outlet(s), (2) M5 x 0.8 female exhaust(s), Cv=0.21, 24 VDC, 0.95W, 9.4mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/100815015321002>

Technical Specifications

Brand	Mindman
Item	Valve
Working Fluid	Air
Valve Type	Solenoid directional control
Port Quantity	5-port (4-way)
Number Of Positions	2
Action	Single solenoid internal pilot return
Body Material	Aluminum
Body Width	15mm
Seal Material	Nitrile
Mounting	Optional manifold
Inlet Port	M5 x 0.8 female

Outlet Port	(2) M5 x 0.8 female
Exhaust Port	(2) M5 x 0.8 female
Manual Override Type	Locking
Flow Coefficient	0.21
Maximum Operating Pressure	116 psi
Minimum Operating Pressure	22 psi
Working Fluid Temperature	-5 to +50 °C (23-122 °F)
Operating Voltage	24 VDC
Power Rating	0.95W
Electrical Connection	9.4mm DIN style wiring plug
Indicating Type	LED indication
Manufacturer Part Number	MVSC1-150-4E1-DC24-L

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/100815015321002.pdf>
See store item page for other formats.