

# 101026USRO Cut Sheet



RUKO step drill bit set, 3 pieces, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/101026USRO>

## Technical Specifications

<b>Brand</b>	RUKO
<b>Item</b>	Drill bit set
<b>Number of Pieces</b>	3
<b>Material</b>	High-speed steel (HSS)
<b>Drill Bit Type</b>	Step
<b>Drill Bit Size</b>	1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in, 1/2in, 9/16in, 5/8in, 11/16in and 3/4in
<b>Number Of Hole Sizes</b>	13, 6 and 9
<b>Step Drill Size</b>	#1, #2 and #3
<b>Finish</b>	Bright
<b>Point Angle</b>	118 degrees
<b>Point Cut</b>	Split
<b>Shank Type</b>	1/4in diameter 3-surface and 3/8in diameter 3-surface
<b>Set Includes</b>	(1) #1 HSS bright coated step drill bit with 1/4in diameter 3-surface shank (1/8, 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 13/32, 7/16, 15/32, 1/2in), (1) #2 HSS bright coated 6 step drill bit with 1/4in diameter 3-surface shank (3/16, 1/4, 5/16, 3/8, 7/16, 1/2in), (1) #3 HSS bright coated 9 step drill bit with 1/4in diameter 3-surface shank (1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4in), heavy duty plastic case
<b>Application</b>	Hole cutting
<b>For Use On</b>	Aluminum, brass, plastic, steel, bronze and cast iron

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>