

101026USRO Cut Sheet



RUKO step drill bit set, 3 pieces, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/101026USRO>

Technical Specifications

Brand	RUKO
Item	Drill bit set
Number of Pieces	3
Material	High-speed steel (HSS)
Drill Bit Type	Step
Drill Bit Size	1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in, 1/2in, 9/16in, 5/8in, 11/16in and 3/4in
Number Of Hole Sizes	13, 6 and 9
Step Drill Size	#1, #2 and #3
Finish	Bright
Point Angle	118 degrees

Point Cut	Split
Shank Type	1/4in diameter 3-surface and 3/8in diameter 3-surface
Set Includes	(1) #1 HSS bright coated step drill bit with 1/4in diameter 3-surface shank (1/8, 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 13/32, 7/16, 15/32, 1/2in), (1) #2 HSS bright coated 6 step drill bit with 1/4in diameter 3-surface shank (3/16, 1/4, 5/16, 3/8, 7/16, 1/2in), (1) #3 HSS bright coated 9 step drill bit with 1/4in diameter 3-surface shank (1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4in), heavy duty plastic case
Application	Hole cutting
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document