

101701E Cut Sheet



RUKO step drill bit, 6 steps, 3/16in, 1/4in, 5/16in, 3/8in, 7/16in and 1/2in, split point, 5% cobalt high-speed steel (HSSE-Co5), bright finish, 1/4in diameter 3-surface shank.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/101701E>

Technical Specifications

Brand	RUKO
Item	Drill bit
Replacement	No
Drill Bit Type	Step
Step Drill Size	#2
Number Of Hole Sizes	6
Drill Bit Size	3/16in, 1/4in, 5/16in, 3/8in, 7/16in and 1/2in
Material	5% cobalt high-speed steel (HSSE-Co5)
Finish	Bright
Point Angle	118 degrees
Point Cut	Split
Shank Type	1/4in diameter 3-surface
Overall Length	3.1in (79mm)
For Use On	Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum
Application	Hole cutting

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document