

101701 Cut Sheet



RUKO step drill bit, 6 steps, 3/16in, 1/4in, 5/16in, 3/8in, 7/16in and 1/2in, split point, high-speed steel (HSS), bright finish, 1/4in diameter 3-surface shank.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/101701>

Technical Specifications

Brand	RUKO
Item	Drill bit
Replacement	No
Drill Bit Type	Step
Step Drill Size	#2
Number Of Hole Sizes	6
Drill Bit Size	3/16in, 1/4in, 5/16in, 3/8in, 7/16in and 1/2in
Material	High-speed steel (HSS)

Finish	Bright
Point Angle	118 degrees
Point Cut	Split
Shank Type	1/4in diameter 3-surface
Overall Length	3.1in (79mm)
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Application	Hole cutting

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/101701.pdf>
See store item page for other formats.