101702E Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

RUKO step drill bit, 13 steps, 1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in and 1/2in, split point, 5% cobalt high-speed steel (HSSE-Co5), bright finish, 1/4in diameter 3-surface shank.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/101702E

Technical Specifications

Brand	RUKO
Item	Drill bit
Replacement	No
Drill Bit Type	Step
Step Drill Size	#1
Number Of Hole Sizes	13
Drill Bit Size	1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in and 1/2in
Material	5% cobalt high-speed steel (HSSE-Co5)

Finish	Bright
Point Angle	118 degrees
Point Cut	Split
Shank Type	1/4in diameter 3-surface
Overall Length	3.1in (79mm)
For Use On	Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum
Application	Hole cutting

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document