

# 101704 Cut Sheet



RUKO step drill bit, 12 steps, 3/16in, 1/4in, 5/16in, 3/8in, 7/16in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in, 13/16in and 7/8in, split point, high-speed steel (HSS), bright finish, 3/8in diameter 3-surface shank.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/101704>

## Technical Specifications

<b>Brand</b>	RUKO
<b>Item</b>	Drill bit
<b>Replacement</b>	No
<b>Drill Bit Type</b>	Step
<b>Step Drill Size</b>	#4
<b>Number Of Hole Sizes</b>	12
<b>Drill Bit Size</b>	3/16in, 1/4in, 5/16in, 3/8in, 7/16in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in, 13/16in and 7/8in
<b>Material</b>	High-speed steel (HSS)
<b>Finish</b>	Bright
<b>Point Angle</b>	118 degrees
<b>Point Cut</b>	Split
<b>Shank Type</b>	3/8in diameter 3-surface
<b>Overall Length</b>	3.3in (84mm)
<b>For Use On</b>	Aluminum, brass, plastic, steel, bronze and cast iron
<b>Application</b>	Hole cutting

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>