

101705 Cut Sheet



RUKO step drill bit, 9 steps, 13/32in, 9/16in, 5/8in, 11/16in, 3/4in, 13/16in, 7/8in, 15/16in and 1in, split point, high-speed steel (HSS), bright finish, 3/8in diameter 3-surface shank.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/101705>

Technical Specifications

Brand	RUKO
Item	Drill bit
Replacement	No
Drill Bit Type	Step
Number Of Hole Sizes	9
Drill Bit Size	13/32in, 9/16in, 5/8in, 11/16in, 3/4in, 13/16in, 7/8in, 15/16in and 1in
Material	High-speed steel (HSS)

Finish	Bright
Point Angle	118 degrees
Point Cut	Split
Shank Type	3/8in diameter 3-surface
Overall Length	3.3in (84mm)
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Application	Hole cutting

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/101705.pdf>
See store item page for other formats.