

101706E Cut Sheet



RUKO step drill bit, 5 steps, 7/8in, 1-1/8in, 1-7/32in, 1-1/4in and 1-3/8in, split point, 5% cobalt high-speed steel (HSSE-Co5), bright finish, 3/8in diameter 3-surface shank.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/101706E>

Technical Specifications

| | | | |
|-----------------------------|---|-----------------------|--|
| Brand | RUKO | Finish | Bright |
| Item | Drill bit | Point Angle | 118 degrees |
| Replacement | No | Point Cut | Split |
| Drill Bit Type | Step | Shank Type | 3/8in diameter 3-surface |
| Step Drill Size | #12 | Overall Length | 3.3in (84mm) |
| Number Of Hole Sizes | 5 | For Use On | Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum |
| Drill Bit Size | 7/8in, 1-1/8in, 1-7/32in, 1-1/4in and 1-3/8in | Application | Hole cutting |
| Material | 5% cobalt high-speed steel (HSSE-Co5) | | |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |