

# 101706T Cut Sheet



RUKO step drill bit, 5 steps, 7/8in, 1-1/8in, 1-7/32in, 1-1/4in and 1-3/8in, split point, high-speed steel (HSS), Titanium-Nitride (TiN) coated finish, 3/8in diameter 3-surface shank.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/101706T>

## Technical Specifications

<b>Brand</b>	RUKO
<b>Item</b>	Drill bit
<b>Replacement</b>	No
<b>Drill Bit Type</b>	Step
<b>Step Drill Size</b>	#12
<b>Number Of Hole Sizes</b>	5
<b>Drill Bit Size</b>	7/8in, 1-1/8in, 1-7/32in, 1-1/4in and 1-3/8in
<b>Material</b>	High-speed steel (HSS)

<b>Finish</b>	Titanium-Nitride (TiN) coated
<b>Point Angle</b>	118 degrees
<b>Point Cut</b>	Split
<b>Shank Type</b>	3/8in diameter 3-surface
<b>Overall Length</b>	3.3in (84mm)
<b>For Use On</b>	Steel, brass, plastic, stainless steel, bronze and cast iron
<b>Application</b>	Hole cutting

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>