

101706T Cut Sheet



RUKO step drill bit, 5 steps, 7/8in, 1-1/8in, 1-7/32in, 1-1/4in and 1-3/8in, split point, high-speed steel (HSS), Titanium-Nitride (TiN) coated finish, 3/8in diameter 3-surface shank.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/101706T>

Technical Specifications

Brand	RUKO
Item	Drill bit
Replacement	No
Drill Bit Type	Step
Step Drill Size	#12
Number Of Hole Sizes	5
Drill Bit Size	7/8in, 1-1/8in, 1-7/32in, 1-1/4in and 1-3/8in
Material	High-speed steel (HSS)
Finish	Titanium-Nitride (TiN) coated
Point Angle	118 degrees
Point Cut	Split
Shank Type	3/8in diameter 3-surface
Overall Length	3.3in (84mm)
For Use On	Steel, brass, plastic, stainless steel, bronze and cast iron
Application	Hole cutting

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document