

# 101709E Cut Sheet



RUKO step drill bit, 2 steps, 7/8in and 1-1/8in, split point, 5% cobalt high-speed steel (HSSE-Co5), bright finish, 3/8in diameter 3-surface shank.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/101709E>

## Technical Specifications

<b>Brand</b>	RUKO
<b>Item</b>	Drill bit
<b>Replacement</b>	No
<b>Drill Bit Type</b>	Step
<b>Step Drill Size</b>	#9
<b>Number Of Hole Sizes</b>	2
<b>Drill Bit Size</b>	7/8in and 1-1/8in
<b>Material</b>	5% cobalt high-speed steel (HSSE-Co5)
<b>Finish</b>	Bright
<b>Point Angle</b>	118 degrees
<b>Point Cut</b>	Split
<b>Shank Type</b>	3/8in diameter 3-surface
<b>Overall Length</b>	3.1in (79mm)
<b>For Use On</b>	Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum
<b>Application</b>	Hole cutting

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>