

102-10 Cut Sheet



CHANNELLOCK Classic curved jaw locking pliers, 9.4in (240mm) overall length, integrated wire cutter, lock nut feature and extended release lever.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/102-10>

Technical Specifications

| | |
|-----------------------|---|
| Brand | CHANNELLOCK |
| Series | Classic |
| Item | Locking pliers |
| Pliers Type | Curved jaw |
| Overall Length | 9.4in (240mm) |
| Insulated | No |
| Capacity | 2.48in |
| Application | Gripping and cutting |
| Material | Forged steel |
| Tool Features | Integrated wire cutter, lock nut feature and extended release lever |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |