

103022011324002 Cut Sheet



Mindman pneumatic solenoid stacking valve, 2-port (2-way), 2-position, N.C., single solenoid spring return, (2) 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), Cv=0.04, 24 VDC, 2W, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/103022011324002>

Technical Specifications

Brand	Mindman
Item	Stacking valve
Working Fluid	Air
Valve Type	Solenoid directional control
Port Quantity	2-port (2-way)
Number Of Positions	2
Valve Configuration	N.C.
Action	Single solenoid spring return
Body Material	Aluminum
Body Width	22mm
Seal Material	Nitrile
Inlet Port	(2) 1/8in female NPT

Outlet Port	1/8in female NPT
Manual Override Type	Locking
Flow Coefficient	0.04
Maximum Operating Pressure	102 psi
Minimum Operating Pressure	0 psi
Working Fluid Temperature	-5 to +50 °C (23-122 °F)
Operating Voltage	24 VDC
Power Rating	2W
Electrical Connection	11mm DIN style wiring plug
Indicating Type	LED indication
Manufacturer Part Number	MVDC-220-2E1-DC24-L-NPT

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/103022011324002.pdf>
See store item page for other formats.