

# 103022011524002 Cut Sheet



Mindman pneumatic solenoid stacking valve, 2-port (2-way), 2-position, N.C., single solenoid spring return, (2) 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), Cv=0.04, 110 VAC, 4.4 VA, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/103022011524002>

## Technical Specifications

<b>Brand</b>	Mindman
<b>Item</b>	Stacking valve
<b>Working Fluid</b>	Air
<b>Valve Type</b>	Solenoid directional control
<b>Port Quantity</b>	2-port (2-way)
<b>Number Of Positions</b>	2
<b>Valve Configuration</b>	N.C.
<b>Action</b>	Single solenoid spring return
<b>Body Material</b>	Aluminum
<b>Body Width</b>	22mm
<b>Seal Material</b>	Nitrile
<b>Inlet Port</b>	(2) 1/8in female NPT

<b>Outlet Port</b>	1/8in female NPT
<b>Manual Override Type</b>	Locking
<b>Flow Coefficient</b>	0.04
<b>Maximum Operating Pressure</b>	102 psi
<b>Minimum Operating Pressure</b>	0 psi
<b>Working Fluid Temperature</b>	-5 to +50 °C (23-122 °F)
<b>Operating Voltage</b>	110 VAC
<b>Power Rating</b>	4.4 VA
<b>Electrical Connection</b>	11mm DIN style wiring plug
<b>Indicating Type</b>	LED indication
<b>Manufacturer Part Number</b>	MVDC-220-2E1-AC110-L-NPT

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/103022011524002.pdf>  
See store item page for other formats.