

103022013524003 Cut Sheet



Mindman pneumatic solenoid stacking valve, 3-port (3-way), 2-position, N.C., single solenoid spring return, (2) 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), vent hole exhaust(s), Cv=0.04, 110 VAC, 4.4 VA, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/103022013524003>

Technical Specifications

Brand	Mindman	Outlet Port	1/8in female NPT
Item	Stacking valve	Exhaust Port	Vent hole
Working Fluid	Air	Manual Override Type	Locking
Valve Type	Solenoid directional control	Flow Coefficient	0.04
Port Quantity	3-port (3-way)	Maximum Operating Pressure	102 psi
Number Of Positions	2	Minimum Operating Pressure	0 psi
Valve Configuration	N.C.	Working Fluid Temperature	-5 to +50 °C (23-122 °F)
Action	Single solenoid spring return	Operating Voltage	110 VAC
Body Material	Aluminum	Power Rating	4.4 VA
Body Width	22mm	Electrical Connection	11mm DIN style wiring plug
Seal Material	Nitrile	Indicating Type	LED indication
Inlet Port	(2) 1/8in female NPT	Manufacturer Part Number	MVDC-220-3E1-AC110-L-NPT

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/103022013524003.pdf>
See store item page for other formats.