

103310092041005 Cut Sheet



Mindman air valve manifold, aluminum, clear, 145 psi maximum operating pressure, (4) stations, (2) M5 x 0.8 female ISO inlet(s), (4) M5 x 0.8 female ISO outlet(s), (2) M5 x 0.8 female ISO exhaust(s). For use with MVDY series miniature solenoid valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/103310092041005>

Technical Specifications

Brand	Mindman
Item	Valve manifold
Working Fluid	Pneumatic
Material	Aluminum
Color	Clear
Number of Stations	4
Maximum Operating Pressure	145 psi
Inlet Port	(2) M5 x 0.8 female ISO
Outlet Port	(4) M5 x 0.8 female ISO
Exhaust Port	(2) M5 x 0.8 female ISO
For Use With	MVDY series miniature solenoid valves

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/103310092041005.pdf>
See store item page for other formats.