

106-10061 Cut Sheet



Sumitomo B2 heat shrink tubing, 1/8in trade size, 2:1 shrink ratio, single wall, flexible, black, flame retardant, UL 1581 VW-1, 4ft stick length. Package of 10.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/106-10061>

Technical Specifications

Brand	Sumitomo
Series	B2
Item	Heat shrink tubing
Trade Size	1/8in
Shrink Ratio	2:1
Flexibility	Flexible
Wall Type	Single wall
Outer Wall Material	Irradiated cross-linked polyolefin
Color	Black
Voltage Rating	600V
Supplied Inside Diameter	0.125in (3.2 mm)
Recovered Inside Diameter	0.062in (1.6 mm)

Recovered Wall Thickness	0.02in (0.51 mm)
Dielectric Strength	942 V/mil (37.1 kV/mm)
Shrink Temperature	194 °F (90 °C)
Minimum Temperature	-67 °F (-55 °C)
Maximum Temperature	257 °F (125 °C)
Flame Retardant	Yes
Flammability	UL 1581 VW-1
Length	4ft stick
Quantity per Pack	10
Applicable Standards	UL 224, CSA C22.2 No. 198.1 and SAE-AS23053/4 Class 1, 3
Application	General purpose

Agency Approvals

UL Recognized File #	E48762
CSA File #	LR33298
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement