

# 106002001021004 Cut Sheet



Mindman pneumatic manual valve, 2-port (2-way), 2-position, toggle style actuator, detented, R1/8 male BSPT inlet(s), M5 x 0.8 female ISO outlet(s), Cv=0.1, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/106002001021004>

## Technical Specifications

<b>Brand</b>	Mindman
<b>Item</b>	Valve
<b>Working Fluid</b>	Air
<b>Valve Type</b>	Manual directional control
<b>Port Quantity</b>	2-port (2-way)
<b>Number Of Positions</b>	2
<b>Operator Type</b>	Toggle style actuator
<b>Action</b>	Detented
<b>Body Material</b>	Stainless steel
<b>Seal Material</b>	Nitrile

<b>Mounting</b>	Through panel
<b>Inlet Port</b>	R1/8 male BSPT
<b>Outlet Port</b>	M5 x 0.8 female ISO
<b>Flow Coefficient</b>	0.1
<b>Maximum Operating Pressure</b>	130 psi
<b>Minimum Operating Pressure</b>	0 psi
<b>Working Fluid Temperature</b>	-5 to +60 °C (23-140 °F)
<b>Includes</b>	Mounting hardware
<b>Manufacturer Part Number</b>	MVHA-2V

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/106002001021004.pdf>  
See store item page for other formats.