


106041105034002 Cut Sheet



Mindman pneumatic manual valve, 5-port (4-way), 2-position, pushbutton, spring return, 1/8in female NPT inlet(s), (2) 1/8in female NPT outlet(s), (2) M5 x 0.8 female ISO exhaust(s), Cv=0.31, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/106041105034002>

Technical Specifications

Brand	Mindman
Item	Valve
Working Fluid	Air
Valve Type	Manual directional control
Port Quantity	5-port (4-way)
Number Of Positions	2
Operator Type	Pushbutton
Action	Spring return
Body Material	Aluminum
Seal Material	Nitrile

Mounting	Through panel
Inlet Port	1/8in female NPT
Outlet Port	(2) 1/8in female NPT
Exhaust Port	(2) M5 x 0.8 female ISO
Flow Coefficient	0.31
Maximum Operating Pressure	130 psi
Minimum Operating Pressure	0 psi
Working Fluid Temperature	-5 to +60 °C (23-140 °F)
Includes	Mounting hardware
Manufacturer Part Number	MVHA-41P-NPT

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/106041105034002.pdf>
See store item page for other formats.