

# 106130017154002 Cut Sheet



Mindman pneumatic manual valve, 5-port (4-way), 3-position, center closed, 90 deg hand lever, spring return to center from right or left, 3/8in female NPT inlet(s), (2) 3/8in female NPT outlet(s), (2) 3/8in female NPT exhaust(s), Cv=1.89.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/106130017154002>

## Technical Specifications

<b>Brand</b>	Mindman
<b>Item</b>	Valve
<b>Working Fluid</b>	Air
<b>Valve Type</b>	Manual directional control
<b>Port Quantity</b>	5-port (4-way)
<b>Number Of Positions</b>	3
<b>Valve Configuration</b>	Center closed
<b>Operator Type</b>	90 deg hand lever
<b>Action</b>	Spring return to center from right or left
<b>Body Material</b>	Aluminum

<b>Body Width</b>	30mm
<b>Seal Material</b>	Nitrile
<b>Inlet Port</b>	3/8in female NPT
<b>Outlet Port</b>	(2) 3/8in female NPT
<b>Exhaust Port</b>	(2) 3/8in female NPT
<b>Flow Coefficient</b>	1.89
<b>Maximum Operating Pressure</b>	174 psi
<b>Minimum Operating Pressure</b>	0 psi
<b>Working Fluid Temperature</b>	-5 to +60 °C (23-140 °F)
<b>Manufacturer Part Number</b>	MVHB-300-4TVC-SP-NPT

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/106130017154002.pdf>  
See store item page for other formats.