

106130017154003 Cut Sheet



Mindman pneumatic manual valve, 5-port (4-way), 3-position, center closed, vertical hand lever, spring return to center from right or left, 3/8in female NPT inlet(s), (2) 3/8in female NPT outlet(s), (2) 3/8in female NPT exhaust(s), Cv=1.89.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/106130017154003>

Technical Specifications

Brand	Mindman
Item	Valve
Working Fluid	Air
Valve Type	Manual directional control
Port Quantity	5-port (4-way)
Number Of Positions	3
Valve Configuration	Center closed
Operator Type	Vertical hand lever
Action	Spring return to center from right or left
Body Material	Aluminum
Body Width	30mm

Seal Material	Nitrile
Mounting	Optional manifold
Inlet Port	3/8in female NPT
Outlet Port	(2) 3/8in female NPT
Exhaust Port	(2) 3/8in female NPT
Flow Coefficient	1.89
Maximum Operating Pressure	174 psi
Minimum Operating Pressure	0 psi
Working Fluid Temperature	-5 to +60 °C (23-140 °F)
Manufacturer Part Number	MVHB-300V-4TVC-SP-NPT

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/106130017154003.pdf>
See store item page for other formats.