

106220200044006 Cut Sheet



Mindman pneumatic manual valve, 4-port (4-way), 2-position, rotary lever, detented, 1/4in female NPT inlet(s), (2) 1/4in female NPT outlet(s), 1/4in female NPT exhaust(s), Cv=0.39, panel or surface mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/106220200044006>

Technical Specifications

Brand	Mindman
Item	Valve
Working Fluid	Air
Valve Type	Manual directional control
Port Quantity	4-port (4-way)
Number Of Positions	2
Operator Type	Rotary lever
Action	Detented
Body Material	Aluminum
Seal Material	Nitrile

Mounting	Panel or surface
Inlet Port	1/4in female NPT
Outlet Port	(2) 1/4in female NPT
Exhaust Port	1/4in female NPT
Flow Coefficient	0.39
Maximum Operating Pressure	145 psi
Minimum Operating Pressure	7 psi
Working Fluid Temperature	-5 to +60 °C (23-140 °F)
Includes	Mounting hardware
Manufacturer Part Number	MVHC-202-4H-8A-M-NPT

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/106220200044006.pdf>
See store item page for other formats.