

106230200054005 Cut Sheet



Mindman pneumatic manual valve, 4-port (4-way), 2-position, rotary lever, detented, 3/8in female NPT inlet(s), (2) 3/8in female NPT outlet(s), 3/8in female NPT exhaust(s), Cv=1.61, panel or surface mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/106230200054005>

Technical Specifications

Brand	Mindman
Item	Valve
Working Fluid	Air
Valve Type	Manual directional control
Port Quantity	4-port (4-way)
Number Of Positions	2
Operator Type	Rotary lever
Action	Detented
Body Material	Aluminum
Seal Material	Nitrile

Mounting	Panel or surface
Inlet Port	3/8in female NPT
Outlet Port	(2) 3/8in female NPT
Exhaust Port	3/8in female NPT
Flow Coefficient	1.61
Maximum Operating Pressure	145 psi
Minimum Operating Pressure	7 psi
Working Fluid Temperature	-5 to +60 °C (23-140 °F)
Includes	Mounting hardware
Manufacturer Part Number	MVHC-302-4H-10A-M-NPT

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/106230200054005.pdf>
See store item page for other formats.