

106302 Cut Sheet



RUKO bi-metal hole saw set, 9 pieces, high-speed steel (HSS), hardened steel backer, varied tooth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/106302>

Technical Specifications

Brand	RUKO
Item	Bi-metal hole saw set
Number of Pieces	9
Material	High-speed steel (HSS)
Hole Saw Size	7/8in (22mm), 1-1/8in (29mm), 1-3/8in (35mm), 1-3/4in (44mm), 2in (51mm) and 2-11/16in
Cutting Direction	Right hand
Hardened Steel Backer	Yes

Tooth Density	5 teeth/in
Toothing	Varied tooth
Set Includes	(6) hole saws (7/8, 1-1/8, 1-3/8, 1-3/4, 2 and 2-11/16in), (2) arbor assemblies (A2 and A4), 4mm Allen wrench, heavy-duty plastic case
Application	Hole cutting
For Use On	Aluminum, plastic and steel

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document