

106600000054001 Cut Sheet



Mindman pneumatic shut-off valve, 2-port (3-way), 2-position, hand slide, 3/8in female NPT inlet(s), 3/8in male NPT outlet(s), vent hole exhaust(s), Cv=1.79.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/106600000054001>

Technical Specifications

Brand	Mindman
Item	Valve
Working Fluid	Air
Valve Type	Shut-off
Port Quantity	2-port (3-way)
Number Of Positions	2
Operator Type	Hand slide
Body Material	Aluminum
Seal Material	Nitrile

Inlet Port	3/8in female NPT
Outlet Port	3/8in male NPT
Exhaust Port	Vent hole
Flow Coefficient	1.79
Maximum Operating Pressure	145 psi
Minimum Operating Pressure	7 psi
Working Fluid Temperature	-5 to +60 °C (23-140 °F)
Manufacturer Part Number	MVHS-10A-NPT

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/106600000054001.pdf>
See store item page for other formats.