

# 10700060 Cut Sheet



WERMA audible alarm buzzer, 80 dB at 10cm, 2.4 kHz tone frequency, continuous tone(s), 115-230 VAC, 22mm, panel mount, glass fiber reinforced polyamide housing, black, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/10700060>

## Technical Specifications

|                             |                                  |
|-----------------------------|----------------------------------|
| <b>Brand</b>                | WERMA                            |
| <b>Item</b>                 | Audible alarm buzzer             |
| <b>Loudness Decibel</b>     | 80 dB at 10cm                    |
| <b>Tone Frequency</b>       | 2.4 kHz                          |
| <b>Tone Type</b>            | Continuous                       |
| <b>Touch to Acknowledge</b> | No                               |
| <b>Voltage Rating</b>       | 115-230 VAC                      |
| <b>Barrel Size</b>          | 22mm                             |
| <b>Mounting</b>             | Panel                            |
| <b>Housing Material</b>     | Glass fiber reinforced polyamide |
| <b>Color</b>                | Black                            |
| <b>IP Rating</b>            | IP65                             |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E164155                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |