

10700077 Cut Sheet



WERMA audible alarm buzzer, 80 dB at 10cm, 2.4 kHz tone frequency, continuous tone(s), 115 VAC/VDC, 22mm, panel mount, glass fiber reinforced polyamide housing, black, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/10700077>

Technical Specifications

Brand	WERMA
Item	Audible alarm buzzer
Loudness Decibel	80 dB at 10cm
Tone Frequency	2.4 kHz
Tone Type	Continuous
Touch to Acknowledge	No
Voltage Rating	115 VAC/VDC
Barrel Size	22mm
Mounting	Panel
Housing Material	Glass fiber reinforced polyamide
Color	Black
IP Rating	IP65

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document