

107015 Cut Sheet



RUKO deburring blade, B30, for deburring cross-hole both edges, rotating blade, right hand, high-speed steel (HSS). Package of 10. For use with extendable blade holder for B blades and universal deburring tool handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/107015>

Technical Specifications

Brand	RUKO
Item	Deburring blade
Deburring Blade Manufacturer Number	B30
Blade Type	Rotating
Cutting Direction	Right hand
Material	High-speed steel (HSS)
Regrindable	No
For Use On	Steel, aluminum and plastic
For Deburring	Cross-hole both edges
Quantity per Pack	10
For Use With	Extendable blade holder for B blades and universal deburring tool handle
Additional Information	For simultaneous deburring of inner and outer bores on material up to 5/32in thick

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document