

107026 Cut Sheet



RUKO deburring blade, E100, for deburring straight edges and hole edges, rotating blade, right hand, high-speed steel (HSS), long shank. Package of 10. For use with extendable blade holder for E blades and universal deburring tool handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/107026>

Technical Specifications

Brand	RUKO
Item	Deburring blade
Deburring Blade Manufacturer Number	E100
Blade Type	Rotating
Cutting Direction	Right hand
Material	High-speed steel (HSS)
Shank	Long shank
Regrindable	No
For Use On	Steel, aluminum and plastic
For Deburring	Straight edges and hole edges
Quantity per Pack	10
For Use With	Extendable blade holder for E blades and universal deburring tool handle

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document